

DDX 9160

Partial Discharge (PD) &
Radio Interference Voltage
(RIV) detector

Datasheet



HAEFELY

Current and voltage – our passion

Designed by



General Description

The DDX 9160 is a **lightweight, portable**, highly integrated, versatile PD and RIV detector, accommodating up to four simultaneous PD/RIV and Voltage inputs. It is a fully digital state-of-the-art high-performance PD detector.

The DDX 9160 is modular and fits a wide range of PD detection applications. It can be operated by **battery** or using an external power supply.

Conventional partial discharge measurements according to the latest IEC 60270 or RIV measurement according to the NEMA and CISPR standards are covered. Phase Resolved PD (PRPD) analysis and Data Logger function are possible as well.

Up to 3 stackable unit(s) connected in daisy chain communicate with a Control Software, which handles data acquisition and display PD information, test results and generates reports.

The DDX 9160 increases the laboratory sensitivity as it is equipped with the most flexible digital filters available on the market allowing the measurement frequency band to be shifted into a less noisy range and suppressing frequency-dependent noise.

The reports can be printed or saved to PDF. The software also provides screenshots function for inclusion in other reports. A default report template is included. However, any new template can be provided on request (option).

Features	Advantages
<ul style="list-style-type: none"> User-defined measuring band Unique flexible high order digital filters High-resolution spectrum analyzer with oscilloscope 	<ul style="list-style-type: none"> <input checked="" type="checkbox"/> Reduced ground noise – The built-in frequency spectrum analysis and selectable frequency band let the user optimize the setup quick and easy.
<ul style="list-style-type: none"> Modular design, 1 to 4 channels Easily upgradable Daisy chain support up to 12 detectors 	<ul style="list-style-type: none"> <input checked="" type="checkbox"/> Optimized investment - Unit can be easily upgraded (up to 12 simultaneous PD/RIV readings).
<ul style="list-style-type: none"> Optically decoupled from computer Compact, reliable, and EMC hardened design, IP50 	<ul style="list-style-type: none"> <input checked="" type="checkbox"/> The galvanic isolation - Ensures the full safety of the operating personnel. With the DDX 9160, there is no electrical connection between the control room and the high voltage test room.
<ul style="list-style-type: none"> PRPD (Phase Resolved Partial Discharge) pattern (fingerprinting) Data acquisition and test report generation 	<ul style="list-style-type: none"> <input checked="" type="checkbox"/> PD interpretation – The phase-resolved analysis and recording capabilities allow future data analysis.
<ul style="list-style-type: none"> Software layout flexibility and versatility Dark software mode 	<ul style="list-style-type: none"> <input checked="" type="checkbox"/> Reduced training time – Modern SW makes the use of the device easier than ever. Operators can start using the device in minutes.
<ul style="list-style-type: none"> Simultaneous RIV (NEMA or CISPR) and PD reading 	<ul style="list-style-type: none"> <input checked="" type="checkbox"/> Measuring time reduction – Simultaneous PD and RIV measurement enables users to reduce the testing time

Applications

- Power and distribution transformers
- Instrument transformers
- Rotating machines
- Switchgears (MV/HV/GIS)
- Surge arresters
- Bushings
- Cables
- Power capacitors
- Components testing
- Research and development

Scope of Supply

- PD detector itself
- FiberLink – LC to USB
- 20 m LC fiber optic cable
- Battery with charger
- USB stick with SW
- Manual
- Quick Start Guide
- Rugged transport case
- PD connection accessories set - per channel (2x 0.5 m banana cable, 2x crocodile clamp, 2x fork-to-4mm adapter, 2x 4mm-socket adapter, 1x 2 m BNC cable, 1x BNC (F) – BNC (F) adapter)

Technical Data

PD Measurement	
Input impedance	50 Ω
PD filter (-6 dB)	Frequency range → Bandwidth (Freely selectable) 30 kHz ... 1.5 MHz → 3 kHz ... 1.47 MHz 300 kHz ... 20 MHz → 30 kHz ... 19.7 MHz
Sensitivity	≤ 0.01 pC (together with AKV 9360; frequency integration)
Linearity error	< ± 1 %
Oscilloscope	Freely selectable 1 μs ... 20 ms recording depth @ sample rate of 100 MSps
Spectrum analyzer (FFT)	0 ... 50 MHz with 2.5 kHz resolution
Built-in (internal) measuring impedance (optional)	
PD input	50 Ω, max. 1 A _{RMS} (1.4 A _{pk})
PD input frequency range	20 kHz ... 25 MHz (-6 dB); 10 kHz ... 30 MHz (-20 dB)
Voltage measurement	Current input (shunt); 10 μA _{RMS} ... 1 A _{RMS} - full accuracy; 0.2 μA _{RMS} - sync minimum
Voltage Measurement	
Input voltage range	0.1 ... 283 V _{RMS} (0.14 ... 400 V _{pk}) – full accuracy; 0.2 mV _{RMS} - sync minimum
Frequency range	DC; 10 ... 600 Hz
Input impedance	Nominal 1 MΩ 3 pF (exact value: 968 kΩ ± 0.1 %)
Linearity error	± 0.1 % ± 100 μV (AC); ± 0.1 % ± 1 mV (DC)
Synchronization	Input voltage
RIV Measurement System	
Filter center frequency	Freely selectable (50 kHz ... 2150 kHz)
Filter bandwidth	4.5 kHz (NEMA) and 9 kHz (CISPR)
Sensitivity	< 1 μV (directly at AKV 9360 quadripole input for NEMA/CISPR)
Quasi-peak detector response	NEMA according to NEMA 107:1987, ANSI C63.2:1996 CISPR according to CISPR 16-1-1:2019, CISPR 18-2:2017, NEMA 107:2016, ANSI C63.2:2016
Connectors	
Ethernet	1x RJ45
Fiber-optic	2 x Duplex LC Multimode (OM2)
PD input	1x ... 4x BNC (option)
Voltage input	1x ... 4x BNC (option)
Fiber-link adapter	Fiber-optic, type LC conversion to Ethernet 10/100 (data) and USB 2.0 (power/data)
Environmental Mechanical and Power Supply	
Operating temperature	-20 °C ... +55 °C
Storage temperature	-40 °C ... +85 °C
Humidity	5 ... 95 % r.h., non-condensing
Dimensions (W x D x H)	170 x 250 x 55 mm (6.7 x 9.9 x 2.2 in)
Weight; Protection class	1.3 kg (2.9 lb); IP 50
Power supply specification	90 -140; 195 - 265 V _{AC} , 50/60 Hz to 12 V _{DC} (external; optional)
Battery	Lithium-Ion rechargeable battery; 11.1 V _{DC} , 97.2 Wh, operating time: > 8 h, charging time: < 3 h
PC and Operation System Requirements	
PC configuration	Minimum: Intel Core i5 (3 rd Gen) or better, 4 GB RAM, Ethernet / USB 2.0 Recommended: Intel Core i7 (10 th Gen) or better, 16 GB RAM, Ethernet / USB 2.0
Operating system	Windows 10 or 11, 64-bit
Applicable Standards	
General	IEC 60270:2000+AMD1:2015, IEC-60060 Parts 1&2, IEC-885-2 and 885-3, IEEE Std. 4, 1995, ICEA T-24-380, ASTM D1868-93, ANSI C57.113, ANSI C57.124-91
CE conformity	EMC Directive 2014/30/EU and RoHS Directive 2011/65/EU

Global Presence

EUROPE
HAEFELY AG
Birsstrasse 300
4052 Basel
Switzerland

☎ + 41 61 373 4111
✉ sales@haefely.com

CHINA
HAEFELY AG Representative Office
8-1-602, Fortune Street, No. 67
Chaoyang Road, Beijing 100025
China

☎ + 86 10 8578 8099
✉ sales@haefely.com.cn

INDIA
HAEFELY India Service Office
C/o Pfiffner Instrument Transformers Pvt. Ltd.
176, 178/2 Sarul, Viholi
Nashik 422 010, India.

☎ +1 800 266 4052 (toll free)
✉ sales@haefely.com

This document has been drawn up with the utmost care. We cannot, however, guarantee that it is entirely complete, correct or up to date.
©Copyright HAEFELY/ Subject to change without notice

V2025.02